PICKLE TANK REPAIRED USING BELZONA PLATE BONDING

ID: 5172

Industry: General Industry Customer Location: Automotive Parts Manufacturer, South

Wales, UK

Application: TCC-Tanks and Chemical Containment Application Date: June 2014

Areas

Substrate: Steel with unidentified coating liner
Products: * Belzona 4301 (Magma CR1 Hi-Build) ,

* Belzona 4311 (Magma CR1),

Problem

Corrosion issues prompted the Client to seek a cost effective solution to seal an internal-to-external drainage outlet. A swift application was required to eliminate any uncontrolled discharges of the acid to the internal working area.









Photograph Descriptions

- * Tank location,
- * Pre-start,
- * Area preparation & pre-coated plate,
- * Application completed,

Application Situation

Pickle tank containing 36% Hydrochloric acid, used in the process of decontaminating manufactured car parts through a system of wash baths.

Application Method

The application was carried out in accordance with Belzona Know-How System Leaflet TCC-3. A mild steel plate, coated one side with Belzona 4311, was manufactured prior to attending site. The plate was bonded in place using Belzona 4301 and the edges sealed with further application of Belzona 4311.

Belzona Facts

For more examples of Belzona Know - How In Action, please visit https://khia.belzona.com

ISO 9001:2015 Belzona products are
FS 695214 manufactured under an ISO
ISO 14001:2015 9000 Registered Quality
EMS 695213 Management System.

www.belzona.com



For more examples of Belzona Know - How In Action, please visit https://khia.belzona.com	0.0
Client was very satisfied and committed to a second application on a neighbouring tank some weeks lat	ter.
The Client required a quick, cost effective solution which did not prolong the plant/equipment downtin	